


Amplitude™ Epsilon™ Wipes



Blue cellulose/polyester nonwoven wipes


Amplitude™ Epsilon™ is made of a special grade blue cellulose and polyester hydroentangled to form a wipe with improved cleanliness and excellent sorbency. The cellulose uses a colorfast dye, to minimize color bleeding. Blue color allows for differentiation in critical areas. Good for wet areas requiring spill pickup and cleanup.



Features	Benefits
Colorfast blue dye	<ul style="list-style-type: none"> • Allows for differentiation between wipes used in different areas
Special grade blue hydroentangled cellulose and polyester	<ul style="list-style-type: none"> • Colorfast dyeing coloring minimizes the risk of color bleeding • Hydroentangled to form a wipe with improved
Excellent sorbency	<ul style="list-style-type: none"> • Good for wet areas requiring spill pickup and cleanup

Part No.	Description	Size	Packaging
AMEP0001	Amplitude Epsilon Wipes, Flat stacked	9" x 9" (230 x 230 mm)	300/bag; 12 bags/case
AMEP0002	Amplitude Epsilon Wipes, Flat stacked	12" x 12" (305 x 305 mm)	150/bag; 20 bags/case

Product Information	
Material	• Cellulose/polyester
Construction	• Hydroentangled nonwoven
Packaging materials	• Outer bags (OB1, OB2), low density polyethylene (LDPE)  Case (CS), corrugated fiberboard (PAP) 
Environment	• ISO 5-8 Grade C/D



Technical Data		
Attribute (units)	Typical Value	Test Method
Basis weight, nominal; (g/m ²)	77	Contec Method
Sorbent capacity; (mL/m ²)	300	IEST-RP-CC004.3, Sec. 8.1
Sorptive rate; (seconds)	<1	
Non-volatile residue, NVR		IEST-RP-CC004.3, Sec. 7.1.2
In deionized water; (g/m ²)	0.01	
In isopropyl alcohol; (g/m ²)	0.01	
Specific ions		IEST-RP-CC004.2, Sec. 7.2.2
Sodium; (ppm)	28.0	
Chloride; (ppm)	10.2	
Particles, readily releasable		IEST-RP-CC004.2, Sec. 5.1
Particles ≥ 0.5µm; (x10 ⁶ /m ²)	48.26	
Fibers ≥ 100µm; (x 10 ³ /m ²)	18.0	

Recycle Symbols

- PET 
- HDPE 
- LDPE 
- PP 
- PAP 

Packaging	EA/OB1	OB1/OB2	OB2/CS	EA/CS
AMEP0001	300	1	12	3,600
AMEP0002	150	1	20	3,000

EA = each; OB = outer bag; CS = case

- Notes**
- a) The data shown are typical values and should not be used as product specifications.
 - b) Valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions.
 - c) Current and/or comparison data may be available. Please contact a Contec sales representative for details.
 - d) All of Contec's packaging is compatible with hydrogen peroxide gassing applications.
 - e) These wipes are free of lint and loose fibers, and meet the definition of lint-free/low linting wipes according to the United States Pharmacopoeia Chapter 797 (USP-NF General Chapter <797> Pharmaceutical Compounding -Sterile Preparations) and the Institute of Environmental Sciences and Technology Recommended Practice IEST-RP-CC004.4

Test Methods:

- 1. CTM = Contec Test Method
- 2. IEST-RP-CC004.3 = Evaluating Wiping Materials Used in Cleanroom and Other Controlled Environments, Institute of environmental Sciences and Technology, Rolling Meadows IL.

PDSW026 | 090822 | ETR2697, 2698, 2699

Copyright © 2022 Contec, Inc. All rights reserved.