

CONSTIX® Sealed Foam Swab SF-5

Flexible paddle tip sealed foam swab


CONSTIX® SF-5 sealed foam swab consists of a polyurethane foam bonded to a flex-tip polypropylene handle without the use of adhesives or binders. The polyurethane foam head provides good particle entrapment and removal. The absorbent foam enables solvents, such as isopropanol and ethanol, to be readily sorbed for applications involving solvent delivery or removal. The SF-5 swab is excellent for applying resins and adhesives.





Though compatible with many common solvents, the SF-5 is not recommended for use with ketones such as acetone or MEK.

Features	Benefits
Flexible paddle tip	<ul style="list-style-type: none"> • Provide good surface contact and controlled pressure to surfaces
Absorbent polyurethane foam head	<ul style="list-style-type: none"> • Ideal for solvent delivery or removal

Part No.	Description	Size	Packaging
SF-10	CONSTIX Sealed foam swab	Head dimension: 0.25" x 0.68" (6.4 x 15.24 mm) Handle diameter: 0.125" (3.0 mm) Total length: 6.44" (163 mm)	500/case



Product Information	
Head material	<ul style="list-style-type: none"> • 100 PPI closed-cell polyurethane foam
Handle material	<ul style="list-style-type: none"> • 100% polypropylene
Construction	<ul style="list-style-type: none"> • Thermally sealed and attached
Packaging materials	<ul style="list-style-type: none"> • Outer bags (BG): low density polyethylene (LDPE)  • Case (CS): corrugated fiberboard (PAP) 

Recycle Symbols



Packaging	EA/BG	BG/CS	EA/CS
SF-5	100	5	500

EA = each; BG = bag; CS = case